

M2050, 1/1.8" Monochrome, Teledyne Dalsa Genie Nano 5GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne Dalsa Genie™ Nano 5GigE Power over Ethernet (PoE) Cameras (Front)



Stock **#16-024** 3-4 DAYS

- 1 + **£1,293.70**

ADD TO CART

Qty 1+
£1,293.70

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
5GigE (PoE)

Type:
Monochrome Camera

Manufacturer:
Teledyne Dalsa

Mounting Threads: ¼-20 with Tripod Mount Adapter #34-966
Image Buffer: 450MB
Camera Family: Genie Nano-5GigE
Model Number: Nano-5G-M2050
Imaging Sensor: Sony IMX252
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.8"
Resolution (MegaPixels): 3.20
Pixels (H x V): 2,064 x 1,544
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 7.12 x 5.33
Frame Rate (fps): 187.00
Pixel Depth: 8 bit
Exposure Time: Automatic, Programmable, or via External Trigger
Connector: 5GigE, RJ45 with Screw Locks
Power Supply: Power over Ethernet (PoE) or via GPIO
Power Consumption (W): 9.4 - 9.6
GPIOs: 2 digital input, 3 digital output
Synchronization: Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)
Dimensions (mm): 59 x 44 x 42.6 (includes connectors and lens mount)
Weight (g): 124
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 76.46
Operating Temperature (°C): -20 to +65
Storage Temperature (°C): -40 to +80
GPIO Connector Type: 10-pin Samtec
Machine Vision Standard: GigE Vision v2.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View