

M4020, 1.1" Monochrome, Dalsa Genie Nano GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne Dalsa Genie™ Nano GigE Power over Ethernet (PoE) Cameras



Stock #35-911 3-4 DAYS

[Similar Cameras](#)

-

1

+

£1,971.15

ADD TO CART

Qty 1+
£1,971.15
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Monochrome Camera

Manufacturer:
Teledyne Dalsa

Mounting Threads: 1/4-20 with Tripod Mount Adapter #34-966
Image Buffer: 200MB
Camera Family: Genie Nano-1GigE
Model Number: Nano-M4020
Imaging Sensor: Sony IMX304
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 12.00
Pixels (H x V): 4,112 x 3,012
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 14.19 x 10.39
Frame Rate (fps): 9.70
Pixel Depth: 8/12 bit
Exposure Time: Programmable or via external trigger
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power over Ethernet (PoE) or via GPIO
Power Consumption (W): 3.6 - 4.6 (12VDC External Power Supply) 4.0 - 4.9 (PoE)
GPIOs: 2 digital input, 2 digital output
Synchronization: Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)
Dimensions (mm): 40.6 x 29.0 x 44.0 (includes connectors and lens mount)
Weight (g): 46
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 76.4
Operating Temperature (°C): -20 to +60
Storage Temperature (°C): -40 to +80
GPIO Connector Type: 10-pin Samtec
Machine Vision Standard: GigE Vision v1.2

Regulatory Compliance

RoHS: Compliant
REACH 201: Compliant
Certificate of Conformance: View