



200 x 600mm Sheet of Metal Velvet Foil, No Adhesive

See More by [Acktar](#)



Acktar Light Absorbent Foil



Stock #12-684

3-4 DAYS



1



£261.80

ADD TO CART

Qty 1-5

£261.80

Qty 6+

£235.62

Volume Pricing

[Request Quote](#)

!

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Metal Velvet™

Model Number: MV-20X60-0
Operating Temperature (°C): -196 to +350
Dimensions (mm): 200 x 600
Type: No Adhesive
Coating Thickness (µm): 5 - 7
Foil Thickness (µm): 115
Abrasion Resistance: Light, do not touch
Humidity Resistance: ML-C-48497A
Wavelength Range (µm): 0.3 - 14
Dimensions (cm): 20 x 60

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant