

NIR Flat Top Beam Shaper | πShaper 6_6_NIR

See More by [AdlOptica](#)



Stock #12-691

3-4 DAYS

-

1

+

£4,591.70

ADD TO CART

Qty 1-4

£4,591.70

Qty 5+

£4,132.70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):

1319, 1650

Diameter (mm):

39.00

Entrance Beam Diameter, 1/e² (mm):

5.9 - 6.0

Model Number: πShaper 6_6_NIR
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <250
Wavelength Range (nm): 1100 - 1700
Style: Flat Top
Damage Threshold, By Design: ☐ 20 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 6.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant