

LUCID Vision Labs Phoenix™ PHX120S-MC, Sony IMX304, 12.3 MP, Monochrome Camera

See More by [LUCID Vision Labs™](#)



Stock #11-472

3-4 DAYS

[Similar Cameras](#)



1



£1,495.15

ADD TO CART

Qty 1+

£1,495.15

Volume Pricing

[Request Quote](#)

!

 Prices shown are exclusive of VAT/local taxes

Note:

 This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:

GigE (PoE)

Type:

Monochrome Camera

Manufacturer: Lucid Vision Labs
Mounting Threads: ¼-20 with Tripod Mount Adapter #11-474
Image Buffer: 128MB
Camera Family: Phoenix™
Model Number: PHX120S-MC
Imaging Sensor: Sony IMX304
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 12.30
Pixels (H x V): 4,096 x 3,000
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 14.13 x 10.35
Frame Rate (fps): 10.00
Pixel Depth: 12 bit
Exposure Time: 30µs - 10s
Connector: GigE, RJ45
Power Supply: Power over Ethernet (PoE) or via GPIO with 12-24VDC Power Supply
Power Consumption (W): 3 (External Power Supply) 3.5 (PoE)
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports
Synchronization: Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)
Dimensions (mm): 28 x 28 x 28.4 (excludes connectors and lens mount)
Weight (g): 39
Mount: C-Mount
Housing: Partial
Interface Port Orientation: Back Panel
Dynamic Range (dB): 71.34
Operating Temperature (°C): -20 to +55
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 8-pin JST
Machine Vision Standard: GigE Vision v2.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View