

LUCID Vision Labs Phoenix™ PHX200S-CC, Sony IMX183, 20.0 MP, Color Camera

See More by [LUCID Vision Labs™](#)



Stock **#11-471** 3-4 DAYS

[Similar Cameras](#)

- 1 +

£557.60

ADD TO CART

Qty 1+

£557.60

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer: Lucid Vision Labs
Mounting Threads: ¼-20 with Tripod Mount Adapter #11-474
Image Buffer: 128MB
Camera Family: Phoenix™
Model Number: PHX200S-CC
Imaging Sensor: Sony IMX183
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1"
Resolution (MegaPixels): 20.00
Pixels (H x V): 5,472 x 3,648
Pixel Size, H x V (µm): 2.40 x 2.40
Sensing Area, H x V (mm): 13.13 x 8.76
Frame Rate (fps): 6.00
Pixel Depth: 12 bit
Exposure Time: 30µs - 10s
Connector: GigE, RJ45
Power Supply: Power over Ethernet (PoE) or via GPIO with 12-24VDC Power Supply
Power Consumption (W): 3 (External Power Supply) 3.5 (PoE)
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports
Synchronization: Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)
Dimensions (mm): 28 x 28 x 28.4 (excludes connectors and lens mount)
Weight (g): 39
Mount: C-Mount
Housing: Partial
Interface Port Orientation: Back Panel
Dynamic Range (dB): 71.76
Operating Temperature (°C): -20 to +55
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 8-pin JST
Machine Vision Standard: GigE Vision v2.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View