

# SCHOTT NG11, 0.1 OD, 12.5mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-717** 3-4 DAYS

⊖ 1 ⊕ **£22.10**

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| £22.10   |

|         |
|---------|
| Qty 11+ |
| £19.55  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

Diameter (mm):  
12.50

Optical Density OD (Average):  
0.1 ±0.006 @ 546nm

Glass/Filter Number:  
[SCHOTT NG11](#)

|                                                                  |
|------------------------------------------------------------------|
| <div>Coating:</div> <div>Uncoated</div>                          |
| <div>Index of Refraction <math>n_d</math>:</div> <div>1.50</div> |
| <div>Surface Quality:</div> <div>80-50</div>                     |
| <div>Transformation Temperature (°C):</div> <div>481</div>       |
| <div>Thickness (mm):</div> <div>0.60</div>                       |
| <div>Thickness Tolerance (mm):</div> <div>(nominal)</div>        |
| <div>Transmission (%):</div> <div>79.43 ±1.03% @ 546nm</div>     |
| <div>Type:</div> <div>Neutral Density Filter</div>               |
| <div>Dimensional Tolerance (mm):</div> <div>±0.38</div>          |
| <div>Wavelength Range (nm):</div> <div>400 - 700</div>           |

## Regulatory Compliance

|                                                                        |
|------------------------------------------------------------------------|
| <div>RoHS:</div> <div>Compliant</div>                                  |
| <div>Certificate of Conformance:</div> <div><a href="#">View</a></div> |
| <div>Reach 240:</div> <div>Compliant</div>                             |

---