

SCHOTT NG11, 0.15 OD, 50mm Sq., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-042** In Stock

-

1

+

£79.05

ADD TO CART

Qty 1-10

£79.05

Qty 11+

£69.70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
0.15 ±0.006 @ 546nm

Glass/Filter Number:
[SCHOTT NG11](#)

Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.50
Surface Quality: 60-40
Transformation Temperature (°C): 481
Thickness (mm): 1.10
Thickness Tolerance (mm): (nominal)
Transmission (%): 70.79 ±0.92% @ 546nm
Type: Neutral Density Filter
Width (mm): 50.00
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View