

SCHOTT NG11, 50mm Sq., 1mm Thick, Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



SCHOTT NG Gray Glass Neutral Density (ND) Filters



Stock **#14-104** ☒ In Stock

-

1

+

£79.05

ADD TO CART

Qty 1-10
£79.05

Qty 11+
£69.70

Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
0.14

Glass/Filter Number: SCHOTT NG11
Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.52
Surface Quality: 60-40
Transformation Temperature (°C): 481
Thickness (mm): 1.00 ±0.1
Transmission (%): 72
Transmission Tolerance (%): (nominal)
Type: Neutral Density Filter
Width (mm): 50.00
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Optical Density Tolerance (%): (nominal)

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View