

SCHOTT NG11, 0.3 OD, 12.5mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-646** 3-4 DAYS

-

1

+

£22.10

ADD TO CART

Qty 1-10
£22.10

Qty 11+
£19.55

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Optical Density OD (Average):
0.3 ±0.006 @ 546nm

Glass/Filter Number:
[SCHOTT NG11](#)

Coating: Uncoated
Index of Refraction n_d: 1.50
Surface Quality: 80-50
Transformation Temperature (°C): 481
Thickness (mm): 2.50
Thickness Tolerance (mm): (nominal)
Transmission (%): 50.12 ±0.65% @ 546nm
Type: Neutral Density Filter
Dimensional Tolerance (mm): ±0.38
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
Reach 240: Compliant