


SCHOTT NG4, 0.9 OD, 12.5mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock #16-729 3-4 DAYS

-

1

+

£22.10

ADD TO CART

Qty 1-10

£22.10

Qty 11+

£19.55

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Optical Density OD (Average):
0.9 ±0.03 @ 546nm

Glass/Filter Number:
[SCHOTT NG4](#)

Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 483
Thickness (mm): 1.70
Thickness Tolerance (mm): (nominal)
Transmission (%): 12.59 ±0.76% @ 546nm
Type: Neutral Density Filter
Dimensional Tolerance (mm): ±0.38
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant