

SCHOTT NG4, 0.9 OD, 50mm Sq., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock #16-731

3-4 DAYS

-

1

+

£79.05

ADD TO CART

Qty 1-10

£79.05

Qty 11+

£69.70

Volume Pricing

[Request Quote](#)

!

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):

50.0 x 50.0

Optical Density OD (Average):

0.9 ±0.03 @ 546nm

Glass/Filter Number:

[SCHOTT NG4](#)

Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 483
Thickness (mm): 1.70
Thickness Tolerance (mm): (nominal)
Transmission (%): 12.59 ±0.76% @ 546nm
Type: Neutral Density Filter
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.38
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant