



SCHOTT NG4, 25mm Dia., 1mm Thick, Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



SCHOTT NG Gray Glass Neutral Density (ND) Filters



Stock **#14-087** □ **In Stock**

-

1

+

£35.70

ADD TO CART

Qty 1-10

£35.70

Qty 11+

£31.45

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
0.55

Glass/Filter Number: SCHOTT NG4
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 483
Thickness (mm): 1.00 ±0.1
Transmission (%): 28
Transmission Tolerance (%): (nominal)
Type: Neutral Density Filter
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Optical Density Tolerance (%): (nominal)

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View
