


SCHOTT NG9, 1.6 OD, 25mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-666** CLEARANCE 3-4 DAYS

-

1

+

£23.76

ADD TO CART

Qty 1+

£23.76

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
1.6

Glass/Filter Number:
[SCHOTT NG9](#)

Coating:
Uncoated

Index of Refraction n_d :

1.51
Surface Quality: 80-50
Transformation Temperature (°C): 470
Thickness (mm): 1.10
Thickness Tolerance (mm): (nominal)
Transmission (%): 2.51
Type: Neutral Density Filter
Dimensional Tolerance (mm): ±0.38
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View