


# SCHOTT NG9, 2.6 OD, 12.5mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-653** ☐ In Stock

-

1

+

**£22.10**

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| £22.10   |

|         |
|---------|
| Qty 11+ |
| £19.55  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

Diameter (mm):  
12.50

Optical Density OD (Average):  
2.6 ±0.07 @ 546nm

Glass/Filter Number:  
[SCHOTT NG9](#)

|                                                      |
|------------------------------------------------------|
| <b>Coating:</b><br>Uncoated                          |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.51 |
| <b>Surface Quality:</b><br>80-50                     |
| <b>Transformation Temperature (°C):</b><br>470       |
| <b>Thickness (mm):</b><br>1.90                       |
| <b>Thickness Tolerance (mm):</b><br>(nominal)        |
| <b>Transmission (%):</b><br>0.250 ±0.043% @ 546nm    |
| <b>Type:</b><br>Neutral Density Filter               |
| <b>Dimensional Tolerance (mm):</b><br>±0.38          |
| <b>Wavelength Range (nm):</b><br>400 - 700           |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |

---