

SCHOTT NG4, 1.3 OD, 12.5mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-649** 3-4 DAYS

⊖ 1 ⊕ **£22.10**

ADD TO CART

Qty 1-10
£22.10

Qty 11+
£19.55

Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Optical Density OD (Average):
1.3 ±0.03 @ 546nm

Glass/Filter Number:
[SCHOTT NG4](#)

Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 483
Thickness (mm): 2.50
Thickness Tolerance (mm): (nominal)
Transmission (%): 5.01 ±0.3% @ 546nm
Type: Neutral Density Filter
Dimensional Tolerance (mm): ±0.38
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
