


# SCHOTT NG9, 3.6 OD, 12.5mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-656** □ In Stock

⊖

1

⊕

£22.10

ADD TO CART

Qty 1-10

£22.10

Qty 11+

£19.55

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
12.50

Optical Density OD (Average):  
3.6 ±0.07 @ 546nm

Glass/Filter Number:  
[SCHOTT NG9](#)

|                                                      |
|------------------------------------------------------|
| <b>Coating:</b><br>Uncoated                          |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.51 |
| <b>Surface Quality:</b><br>80-50                     |
| <b>Transformation Temperature (°C):</b><br>470       |
| <b>Thickness (mm):</b><br>2.60                       |
| <b>Thickness Tolerance (mm):</b><br>(nominal)        |
| <b>Transmission (%):</b><br>0.025 ±0.00425% @ 546nm  |
| <b>Type:</b><br>Neutral Density Filter               |
| <b>Dimensional Tolerance (mm):</b><br>±0.38          |
| <b>Wavelength Range (nm):</b><br>400 - 700           |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |

---