



# SCHOTT NG4, 50mm Sq., 3mm Thick, Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



SCHOTT NG Gray Glass Neutral Density (ND) Filters



Stock **#14-090** ☒ In Stock

-

1

+

£79.05

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| £79.05   |

|         |
|---------|
| Qty 11+ |
| £69.70  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):  
50.0 x 50.0

Optical Density OD (Average):  
1.58

|                                                                |
|----------------------------------------------------------------|
| <div>Glass/Filter Number:<br/><a href="#">SCHOTT NG4</a></div> |
| <div>Length (mm):<br/>50.00</div>                              |
| <div>Coating:<br/>Uncoated</div>                               |
| <div>Index of Refraction n<sub>d</sub>:<br/>1.51</div>         |
| <div>Surface Quality:<br/>60-40</div>                          |
| <div>Transformation Temperature (°C):<br/>483</div>            |
| <div>Thickness (mm):<br/>3.00 ±0.2</div>                       |
| <div>Transmission (%):<br/>2.6</div>                           |
| <div>Transmission Tolerance (%):<br/>(nominal)</div>           |
| <div>Type:<br/>Neutral Density Filter</div>                    |
| <div>Width (mm):<br/>50.00</div>                               |
| <div>Parallelism (arcmin):<br/>≤3</div>                        |
| <div>Dimensional Tolerance (mm):<br/>±0.2</div>                |
| <div>Optical Density Tolerance (%):<br/>(nominal)</div>        |

Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Reach 224:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |