



SCHOTT NG5, 25mm Dia., 1mm Thick, Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



SCHOTT NG Gray Glass Neutral Density (ND) Filters



Stock **#14-093** ▢ **In Stock**

-

1

+

£35.70

ADD TO CART

Qty 1-10
£35.70
Qty 11+
£31.45
Volume Pricing
Request Quote
! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
0.28

Glass/Filter Number: <a>SCHOTT NG5
Coating: Uncoated
Index of Refraction n_d: 1.50
Surface Quality: 60-40
Transformation Temperature (°C): 474
Thickness (mm): 1.00 ±0.1
Transmission (%): 53
Transmission Tolerance (%): (nominal)
Type: Neutral Density Filter
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Optical Density Tolerance (%): (nominal)

Regulatory Compliance

RoHS: <a>Compliant
Certificate of Conformance: <a>View