

T-Mount Electrical Shutter



T-Mount Electrical Shutter (#11-153)

Stock #11-153 3-4 DAYS



1



£547.40

ADD TO CART

Qty 1-4

£547.40

Qty 5+

£484.75

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Outer Diameter (mm):
69.0

Activation Time (ms):
90

Aperture (mm):
30.0

Coil Resistance (Ω): 90 @ 25°C
Coil Resistance Tolerance (%): ±10
Deactivation time (ms): 50
Mount: T-Mount
Operating Temperature (°C): -10 to +60
Operating Voltage (V): 4.5 V ~ 5.5 VDC
Weight (g): 100
Function: Shutter
Thread Type: T-Mount
Operating Frequency (Hz): 7 (full open/close), 30 (partial open/close)
Operating Life Cycle: 100,000
Compatible Post: M6 x 1.0, ¼-20
Extension Length (mm): 16.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View