

VIS Flat Top Beam Shaper | πShaper 6_6_VIS

See More by [AdlOptica](#)



Stock #12-644 3-4 DAYS

- 1 + **£5,051.55**

ADD TO CART

Qty 1-4
£5,051.55

Qty 5+
£4,548.35

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
442, 632.8

Diameter (mm):
39.00

Entrance Beam Diameter, 1/e² (mm):
6.0

Model Number: πShaper 6_6_VS
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <270
Wavelength Range (nm): 405 - 680
Style: Flat Top
Damage Threshold, By Design: ☐ 20 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 6.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant