

BFS-U3-13Y3M-C USB 3.1 Blackfly® S, Monochrome Camera

See More by [Teledyne FLIR](#)



FLIR Blackfly® S USB3 Camera (front)



Stock #36-451 3-4 DAYS

[Similar Cameras](#)

1 £408.00

ADD TO CART

Qty 1+

£408.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type:

Monochrome Camera

Manufacturer:
FLIR

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#88-210](#)

Image Buffer:
240MB

Camera Family:
Blackfly® S

Model Number:
BFS-U3-13Y3M-C

Imaging Sensor:
ON Semi PYTHON 1300

Type of Sensor:
Progressive Scan CMOS

Type of Shutter:
Global

Camera Sensor Format:
1/2"

Resolution (MegaPixels):
1.30

Pixels (H x V):
1,280 x 1,024

Pixel Size, H x V (µm):
4.8 x 4.8

Sensing Area, H x V (mm):
6.14 x 4.92

Frame Rate (fps):
170.00

Pixel Depth:
10 bit

Exposure Time:
6µs - 30s

Connector:
USB 3.1 Gen 1, Micro-B with Screw Locks

Power Supply:
Power over USB or via GPIO with [#88-063](#)

Power Consumption (W):
Not Specified

GPIOs:
1 opto-isolated input, 1 opto-isolated output, 1 non-isolated bi-directional, 1 non-isolated input

Synchronization:
Hardware Trigger (GPIO) or Software Trigger

Dimensions (mm):
29 x 29 x 30 (excludes connectors and lens mount)

Weight (g):
36

Mount:
C-Mount

Housing:
Full

Interface Port Orientation:
Back Panel

Dynamic Range (dB):
54.61

Operating Temperature (°C):
0 to +50

Storage Temperature (°C):
-30 to +60

GPIO Connector Type:
6-pin Hirose (HR10)

Machine Vision Standard:
USB3 Vision v1.0

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)

