

Ti:Sapphire Flat Top Beam Shaper | πShaper 6_6_TiS

See More by [AdlOptica](#)



Ti:Sapphire Flat Top Beam Shaper, #36-649

Stock **#36-649** 3-4 DAYS

-

1

+

£5,051.55

ADD TO CART

Qty 1-4
£5,051.55
Qty 5+
£4,548.35
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
800

Diameter (mm):
39.00

Entrance Beam Diameter, 1/e² (mm):
6.4 - 6.5

Model Number: πShaper 6_6_TIS
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <270
Wavelength Range (nm): 700 - 900
Style: Flat Top
Damage Threshold, By Design: ☐ 20 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 6.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant