

LightPath 390010 | 8.24mm Dia., 0.83 NA, BBAR (8000-12000nm), Mounted IR Aspheric Lens

See More by [Lightpath®](#)



Stock **#88-079** CLEARANCE 3-4 DAYS

[Other Coating Options](#)



1



£146.16

ADD TO CART

Qty 1+

£146.16

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
8.24 ±0.10

Effective Focal Length EFL (mm):
1.47 @ 9200nm

Numerical Aperture NA:
0.83

Substrate:  Black Diamond™ BD-2 (Ge₂₈Sb₁₂Se₆₀)
Aspheric Design Wavelength (nm): 9200
Coating: BBAR (8000-12000nm)
Coating Specification: R_{avg} <1.0% @ 8 - 12μm
Surface Quality: 80-50
Clear Aperture CA (mm): 3.00
Center Thickness CT (mm): 2.17
f/#: 0.6
Bevel: Protective bevel as needed
Density (g/cm³): 4.68
Index of Refraction n_d @ 10μm: 2.6023
Index of Refraction n_d @ 14μm: 2.5843
Index of Refraction n_d @ 4μm: 2.6210
Index of Refraction n_d @ 5μm: 2.6173
Lightpath Lens Code: 390010
Mount: Stainless Steel, M8 x0.5 Thread
Thermo-optic coefficient dn/dT: 70 x 10⁻⁶/°C from -40° to +80°C (5 - 14 μm)
Transformation Temperature (°C): 285.00
Type: Aspheric Lens
Wavelength Range (nm): 8000 - 12000
Working Distance (mm): 0.63
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant