

VZM™ 100i Zoom Imaging Lens



VZM™ 100i

Stock #59-805 3-4 DAYS



1



£952.00

ADD TO CART

Qty 1+

£952.00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
151.70

Horizontal Field of View, 1/2" Sensor:
25.6 - 6.4mm

Horizontal Field of View, 2/3" Sensor:
35.2 - 8.8mm

Filter Thread:
M22.5 x 0.50

Maximum Diameter (mm):

30.00
Weight (g): 270.00
Working Distance Tolerance (mm): ±3
Resolution, Object Space: 17.5 lp/mm - 32 lp/mm
Resolution, Image Space: 70 lp/mm - 32 lp/mm
Zoom Ratio: 4:1
Type: Zoom Lens
Primary Magnification PMAQ: 0.25X - 1X
Maximum Sensor Format: 2/3"
Working Distance (mm): 175.00
Mount: C-Mount
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View