

TECHSPEC®

125mm X-Y Positioning Stage



125mm X-Y Positioning Stage

Stock #12-694 ▢ In Stock



1



£461.55

ADD TO CART

Qty 1-4

£461.55

Qty 5+

£407.66

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X-Y)

Guide System:
Ball Slide

Type of Drive:
Rack and Pinion

Drive Orientation: Center Drive
Type: Universal
Travel (mm): 70 (±35mm) in X and Y
Travel (inches): 2.75 (±1.37) in X and Y
Load Capacity, Normal (kg): 10
Mounting Threads: (4) M4 x 0.7
Note: Movement
Straight Line Accuracy (µm): 60
Travel Per Knob Rotation (mm): 18

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View