


NOTES:

- 1. ALLOWABLE OPTICAL MATERIAL: GRADE A FINE ANNEALED
SCHOTT: Fused Silica 458/678
- 2. CENTERING TOLERANCE:
BEAM DEVIATION: 3-5 arc min.
- 3. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: NONE
- 4. FINE GROUND SURFACE
- 5. FOCAL LENGTH TOLERANCE: $\pm 2\%$



FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING

	S1	S2			 Edmund Optics®	
SHAPE	CONCAVE	PLANO	EFL (AT 587.6nm)	-100.00		
RADIUS	-45.84	INFINITY	BFL (AT 587.6nm)	-102.40	TITLE	LENS PCV-UV 50.8MM DIA X -100MM FL UNCOATED
SURFACE QUALITY	40-20	40-20	ALL DIMS IN	mm	DWG NO	08031
CLEAR APERTURE	49.80	49.80				
BEVEL MAX FACE	0.3mm x 45°	0.3mm x 45°				