

TECHSPEC[®] Finite Conjugate, Gold Coated, 15X/0.28NA HP ReflX



High Performance ReflX™ Objectives

Stock #59-889 [CONTACT US](#)

-

1

+

£2,187.90

ADD TO CART

Qty 1+

£2,187.90

Qty 2+

£1,968.60

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Entrance Pupil Position (mm):
40.0

Field of View (mm):
150

Horizontal Field of View, 1/2" Sensor:
0.43mm

Horizontal Field of View, 2/3" Sensor: 0.59mm
Focal Length FL (mm): 12.97
Coating: Protected Gold (700-11000nm)
Magnification: 15X
Mount: RMS
Numerical Aperture NA: 0.28
Type: Microscope Objective
Obscuration (%): 27.00
Transmitted Wavefront, RMS: λ/14
Diameter of Small Mirror (mm): 8.8
Working Distance (mm): 23.75
Aperture Diameter (mm): 8.5
Note: Entrance Pupil Position specification is measured in mm from flange
Coating Specification: Ravg >96% @ 700 - 11000nm (typical)
Wavelength Range (nm): 700 - 11000
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Flange Distance (mm): 150

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View