


TECHSPEC® SWIR IMAGING LENSES



- Designed, Coated, and Tested for SWIR Wavelengths
- Compact, Lightweight, COTS Imaging Lenses
- Low f/# for High Throughput

Designed for the short-wave infrared (SWIR) wavelengths, 0,9 - 1,7 μm , TECHSPEC® SWIR Fixed Focal Length Imaging Lenses are a compact, lightweight solution for SWIR imaging applications, including inspection, sorting, and quality control. TECHSPEC® SWIR Fixed Focal Length Imaging Lenses are anti-reflection (AR) coated from 800 nm - 1,8 μm and are designed to cover large, 25 mm sensors. These commercial off-the-shelf lenses (COTS) have low f/#s for high throughput and improved performance.



M42 x 1,0 Mounting Adapter for 25 mm Lens #83-151

TECHSPEC® SWIR FIXED FOCAL LENGTH IMAGING LENSES								*Horizontal
Focal Length	Max. Sensor Diagonal	FOV Range on Max. Sensor	FOV* on 20,5 mm Sensor	Working Distance	Aperture (f/#)	Weight	Mount	Stock Number
25 mm	25,6 mm	206,8 - 55,8°	128,2 - 35,5°	200 mm - ∞	f2,1 - f16	180 g	C-Mount	#83-160
50 mm	25,6 mm	140,7 mm - 29°	112,3 mm - 23,3°	275 mm - ∞	f2,25 - f22	566 g	C-Mount	#83-165
50 mm	25,6 mm	140,7 mm - 29°	112,3 mm - 23,3°	275 mm - ∞	f2,25 - f22	482 g	F-Mount	#83-166
50 mm	25,6 mm	140,7 mm - 29°	112,3 mm - 23,3°	275 mm - ∞	f2,25 - f22	574 g	M42 x 1,0	#83-167

DIMENSIONS (mm)						
Focal Length	A	B	C	D	Filter Thread	
25 mm, C-Mount	40	63,5	40	7,62	M34 x 0,50	
50 mm, C-Mount	56	112	55	0	M43 x 0,75	
50 mm, F-Mount	56	103	55	28	M43 x 0,75	
50 mm, M42 x 1,0	56	124	55	0	M43 x 0,75	

WANT TO LEARN MORE? VISIT WWW.EDMUNDOPTICS.EU/SWIR



www.edmundoptics.eu/swir

Contact us for a Volume Quote Today!

UK: +44 (0) 1904 788600 GERMANY: +49 (0) 721 6273730
 sales@edmundoptics.eu FRANCE: +33 (0) 8 20 20 75 55

SWIR IMAGING APPLICATIONS

WHAT IS SWIR?

Short-Wave Infrared (SWIR) light is typically defined as light in the 0,9 - 1,7 μm wavelength range, but can also be classified from 0,7 – 2,5 μm . Since silicon sensors have an upper limit of approximately 1,0 μm , SWIR imaging requires unique components capable of performing in the SWIR range. Indium Gallium Arsenide (InGaAs) sensors are the primary sensors used in SWIR, covering the typical SWIR band, but can extend as low as 550 nm to as high as 2,5 μm . Although linear line-scan InGaAs sensors are commercially available, area scan InGaAs sensors are typically ITAR restricted, but are available for a number of commercial applications with proper licenses. SWIR imaging lenses are specially designed, optimized, and anti-reflection coated for SWIR wavelengths.

WHY USE SWIR?

Unlike Mid-Wave Infrared (MWIR) and Long-Wave Infrared (LWIR) light, which is emitted from the object itself, SWIR is similar to visible light in that photons are reflected or absorbed by an object, providing the strong contrast needed for higher resolution imaging. Ambient star light and background radiance (nightglow) are natural emitters of SWIR and provide excellent illumination for outdoor, nighttime imaging.

SWIR APPLICATIONS

- **Electronic Board Inspection**
- **Solar Cell Inspection**
- **Identifying and Sorting**
- **Produce Inspection**
- **Surveillance**
- **Anti-Counterfeiting**
- **Process Quality Control**



Visible Image



SWIR Image

The Last Judgment by Jan Provost and imaged in the SWIR waveband by the Detroit Institute of Arts, details the artist's original intention by carefully examining the underdrawing which lies beneath the paint film. One can see 10 trumpets underneath the archangel versus the 5 trumpets that were actually painted. The placement of the painted trumpets appears to have necessitated a reposition of the sailing vessel. The toes on top of the globe were also not painted in the same location as the original underdrawing.



*Images Copyright©
by Detroit Institute of Arts.
Used with permission.*