NOTES:

- 1. SUBSTRATE: N-BK7
- 2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION: ≤2 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE):


\$1, \$2, \$3, & \$4: R(AVG) <0.5% @ 430 - 670nm \$5: MULTILAYER DIELECTRIC TO ACHIEVE: TRANSMISSION > 45% ± 5%


POLARIZATION < 6%

FINE GROUND SURFACE

ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61

/6.\ MARK IDENTIFIES BEAMSPLITTED COATED RIGHT ANGLE PRISM





FOR INFORMATION ONLY:

PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2 PLANO 1/8 WAVE	
SHAPE	PLANO		
SURFACE ACCURACY	1/8 WAVE		
SURFACE QUALITY	40-20	40-20	
CLEAR APERTURE	> 90%	> 90%	

			Edmund Optics®
THIRD ANGLE PROJECTION	$\phi \Box$	TITLE	12.5mm VIS, Non-Polarizing Cube Beamsplitter
ALL DIMS IN	mm	DWG NO	49003 SHEET 1 OF 1