NOTES:


SUBSTRATE: FUSED SILICA


2. RoHS: COMPLIANT

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN

4. COATING (APPLY ACROSS COATING APERTURE) \$1& \$2: R(ABS) ≤0.25% @ 880nm R(AVG) ≤1.25% FROM 400 - 870nm R(AVG) ≤1.25% FROM 890 - 1000nm







PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	\$1 PLANO	S2 PLANO				Edmund Option	CS [®]
SURFACE ACCURACY	1λ	1λ		1		15mm DIA VIS NIB COATED 1) EUSED	SILICA
SURFACE QUALITY	60-40	60-40	THIRD ANGLE PROJECTION		TITLE	15mm DIA. VIS - NIR COATED, 1λ FUSED SILICA WINDOW	
CLEAR APERTURE	Ø13.50	Ø13.50				THINDOW	CHEET
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	49641	SHEET 1 OF 1

