


TECHSPEC® Achromatic Lenses


Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



+ 0.4861
x 0.5876
■ 0.6563



SURFACE: INA

DIA: 0.000 MM

SPOT DIAGRAM

49785INK
TUE DEC 16 2008 UNITS ARE μm.
FIELD :
RMS RADIUS : 82.157
GD RADIUS : 191.760
SCALE BAR : 400


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT

49785INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 182.9642 μm
DIFFRACTION LIMITED RANGE: 5.464 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM




OBJ: 0.0000 DEG

TRANSVERSE RAY FAN PLOT

49785INK
TUE DEC 16 2008
MAXIMUM SCALE: ± 500.000 μm.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



POLYCHROMATIC DIFFRACTION MTF

49785INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

EO Edmund
optics | worldwide

www.edmundoptics.com