





☒ + 0.486133
☒ 0.587562
☒ 0.656273



Surface: IMA

Spot Diagram

67333
 4/21/2017
 Units are μm.
 Field : 1
 RMS radius : 4.197
 GEO radius : 9.361
 Scale bar : 40
 Airy Radius: 13.77 μm. Legend items refer to Wavelengths
 Reference : Chief Ray

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

67333.ZMX
 Configuration 1 of 1



Chromatic Focal Shift

67333
 4/21/2017
 Maximum Focal Shift Range: 564.7472 μm
 Diffraction Limited Range: 867.540 μm
 Pupil Zone: 0.0000

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

67333.ZMX
 Configuration 1 of 1

OBJ: 0.0000 (deg)



☒ Diff. Limit-Tangential ☒ Diff. Limit-Sagittal
☒ 0.0000 (deg)-Tangential ☒ 0.0000 (deg)-Sagittal

Transverse Ray Fan Plot

67333
 4/21/2017
 Maximum Scale: ± 20.000 μm.
 0.486 0.588 0.656
 Surface: Image

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

67333.ZMX
 Configuration 1 of 1

Polychromatic Diffraction MTF

67333
 4/21/2017
 Data for 0.4861 to 0.6563 μm.
 Surface: Image

Legend items refer to Field positions

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

67333.ZMX
 Configuration 1 of 1