


NOTES:

1. SUBSTRATE MATERIAL:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2:
LASER V-COAT



R(abs) <0.25% @ 405nm
R(avg) <1.5% @ 375 - 435nm

3. FINE GROUND SURFACE
4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | | | | | | | |
|------------------|---------------------|---------------------|---|---------|--|---|-----------------|
| REV. A | S1 | S2 | | | | | |
| SHAPE | CONVEX | PLANO | EFL | 75±3% |  Edmund Optics® | | |
| RADIUS | 38.76 | ∞ | BFL | (73.68) | | | |
| SURFACE QUALITY | 60-40 | 60-40 |  | | TITLE | 12.5mm DIA X 75.0mm FL 405nm V-COAT, CYLINDER LENS | |
| CLEAR APERTURE | Ø 11.50 | Ø 11.50 | | | | | |
| COATING APERTURE | Ø 11.50 | Ø 11.50 | | | | | |
| BEVEL | PROTECTED AS NEEDED | PROTECTED AS NEEDED | ALL DIMS IN | mm | DWG NO | 33217 | SHEET 1 OF 1 |