

NOTES:

- SUBSTRATE: GRADE A FINE ANNEALED
SCHOTT: N-BK7 517/642
- ROHS COMPLIANT
- SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3
ARCMIN
- COATING (APPLY ACROSS COATING APERTURE)
SPECIFICATIONS AT 45° AOI AND RANDOM POLARIZATION
S1:
 $R(\text{abs}) = 30\% \pm 5\% @ 550\text{nm}$
 $R(\text{abs}) = 30\% \pm 10\% \text{ FROM } 400\text{-}700\text{nm}$
 $T(\text{abs}) = 70\% \pm 5\% @ 550\text{nm}$
 $T(\text{abs}) = 70\% \pm 10\% \text{ FROM } 400\text{-}700\text{nm}$
 VISUAL COLOR = NEUTRAL

S2: BBAR


$R(\text{abs}) \leq 2.0\% \text{ FROM } 400\text{-}700\text{nm}$
 $R(\text{avg}) \leq 1.0\% \text{ FROM } 400\text{-}700\text{nm}$



FINE GRIND SURFACE



MARK IDENTIFIES BEAMSPLITTER SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

	S1	S2
SHAPE	PLANO	PLANO
SURFACE ACCURACY AT 632.8nm (P-V)	1 WAVE	1 WAVE
SURFACE QUALITY	60 - 40	60 - 40
SURFACE FLATNESS	2λ PER 25mm	2λ PER 25mm
MIN CLEAR APERTURE	Ø 10.63	Ø 10.63
MIN COATING APERTURE	Ø 10.63	Ø 10.63
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics**®

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

TITLE	BS VIS 30R/70T 12.5mm DIA 1MM THK	
DWG NO	35931	SHEET 1 OF 1