

NOTES:

1. SUBSTRATE: GRADE A FINE ANNEALED
SCHOTT: N-BK7 517/642
2. ROHS COMPLIANT
3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN
4. COATING (APPLY ACROSS COATING APERTURE)
SPECIFICATIONS AT 45° AOI AND RANDOM POLARIZATION
S1:
 $R(\text{abs}) = 30\% \pm 5\% @ 550\text{nm}$
 $R(\text{abs}) = 30\% \pm 10\% \text{ FROM } 400\text{-}700\text{nm}$
 $T(\text{abs}) = 70\% \pm 5\% @ 550\text{nm}$
 $T(\text{abs}) = 70\% \pm 10\% \text{ FROM } 400\text{-}700\text{nm}$
 VISUAL COLOR = NEUTRAL


S2: BBAR
 $R(\text{abs}) \leq 2.0\% \text{ FROM } 400\text{-}700\text{nm}$
 $R(\text{avg}) \leq 1.0\% \text{ FROM } 400\text{-}700\text{nm}$



FINE GRIND SURFACE



MARK IDENTIFIES BEAMSPLITTER SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

	S1	S2
SHAPE	PLANO	PLANO
SURFACE ACCURACY AT 632.8nm (P-V)	1 WAVE	1 WAVE
SURFACE QUALITY	60 - 40	60 - 40
SURFACE FLATNESS	2λ PER 25mm	2λ PER 25mm
MIN CLEAR APERTURE	10.63 x 14.88	10.63 x 14.88
MIN COATING APERTURE	10.63 x 14.88	10.63 x 14.88
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®



THIRD ANGLE
PROJECTION

TITLE

BS VIS 30R/70T 12.5X17.5MM 1MM THK

ALL DIMS IN

mm

DWG NO

35932

SHEET
1 OF 1