



NOTES:

1. SUBSTRATE: FUSED SILICA
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: R(avg) ≤1.5% @ 250 - 450nm
S2: R(avg) ≤1.5% @ 250 - 450nm
3. EDGES: FINE GROUND
4. CENTERING: <3-5 ARCMIN
5. ASPHERE FIGURE ERROR: 0.75μm RMS

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

6.  ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)


$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



SECTION A-A

COEFFICIENT TABLE 	
COEFFICIENT	S1
k	-1.123452E+00
D	0
E	3.801254E-04
F	2.946223E-06
G	-1.655839E-08
H	0 5.349691E-10
J	0
L	0

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL @ 587.6nm	12.5	 Edmund Optics®	
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	6.33		
RADIUS	5.731	INFINITY			TITLE	15mm DIA 0.60 NA UV COATED, UV FUSED SILICA ASPHERIC LENS
SURFACE QUALITY	60-40	60-40			DWG NO	67269
CLEAR APERTURE	90%	90%	ALL DIMS IN	mm		SHEET 1 OF 1
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				