


NOTES:

1. SUBSTRATE: FUSED SILICA
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: R(avg) ≤1.5% @ 600 - 1050nm
S2: R(avg) ≤1.5% @ 600 - 1050nm
3. EDGES: FINE GROUND
4. CENTERING: <3-5 ARCMIN
5. ASPHERE FIGURE ERROR: 0.75µm RMS

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



SECTION A-A

COEFFICIENT TABLE 7	
COEFFICIENT	S1
k	-1.471923E+00
D	0
E	5.474309E-06
F	-2.150776E-10
G	4.540082E-13
H	-3.526000E-18
J	0
L	0

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL @ 587.6nm	60	 Edmund Optics®			
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	48.34				
RADIUS	27.508	INFINITY	<div>THIRD ANGLE PROJECTION</div> 		TITLE	50mm DIA 0.42 NA NIR COATED, UV FUSED SILICA ASPHERIC LENS		
SURFACE QUALITY	60-40	60-40						
CLEAR APERTURE	90%	90%	<div>ALL DIMS IN</div> <div>mm</div>		DWG NO	67283		SHEET 1 OF 1
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED						