




NOTES:


1. SUBSTRATE MATERIAL:  
FUSED SILICA
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: ULTRAFAST LASER  
R<sub>avg</sub> ≥ 99.5% REFLECTIVITY AT 750 - 850nm AT 0° AOI  
S2: NONE
3. FINE GROUND SURFACE
4. RoHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE ACCURACY AT 632.8nm (P-V)	$\lambda/6$	N/A
SURFACE QUALITY	10 - 5	COMMERCIAL POLISH
CLEAR APERTURE	Ø21.59	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: 800nm, 25.4mm Dia. x 9.52mm Thickness, 0° Ultrafast Broadband Mirror

DWG NO: 36405

SHEET 1 OF 1