
## NOTES:


- SUBSTRATE: UV GRADE FUSED SILICA 1.
- 2. COATING (APPLY ACROSS COATING APERTURE) S1 & S2: RABS ≤1.0% @ 250 - 425nm RAVG ≤0.75% @ 250 - 425nm RAVG ≤0.5% @ 370 - 420nm
- SURFACE S2 TO BE PARALLEL TO SURFACE \$1 WITHIN <5 ARCSEC 3.

**∕**4.∖

FINE GRIND SURFACE

5. **ROHS COMPLIANT** 





## PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	20-10	20-10	
CLEAR APERTURE	Ø60.00	Ø60.00	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

		<b>Edmund Optics</b> ®		
HIRD ANGLE PROJECTION		TITLE	75mm DIA., 5mm THICK, UV-AR COATED FUSED SILICA WINDOW	λ/10
ALL DIMS IN	mm	DWG NO	36963	SHEET 1 OF

75mm DIA., 5mm THICK, UV-AR COATED λ/1	10
fused silica window	

SHEET 1 OF 1