



NOTES:

1. SUBSTRATE:
B270

2. COATING

S1: NONE
S2: NONE
S3: NONE


3. EDGES: FINE GROUND



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	S3
SHAPE	PLANO	PLANO	PARABOLIC
RADIUS	∞	∞	ASPHERIC
SURFACE QUALITY	80-50	80-50	(80-50)
CLEAR APERTURE	$\varnothing 2.13$	$\varnothing 7.52$	N/A
BEVEL MAX	PROTECTIVE AS NEEDED		NONE

THIRD ANGLE PROJECTION 		Edmund Optics®	
		TITLE	45°, 5.0mm OUTPUT DIA., COMPOUND PARABOLIC CONCENTRATOR
ALL DIMS IN	mm	DWG NO	65444
			SHEET 1 OF 1