

NOTES:


- 1. SUBSTRATE MATERIAL: FLOAT GLASS
- 2. COATING (APPLY ACROSS CLEAR APERTURE): S1: BARE ALUMINUM S2: NONE
- 3. WAVELENGTH RANGE: 400-700nm ABSOLUTE DIFFRACTION EFFICIENCY: 45-65% GROOVE DENSITY: 1200 grooves/mm



5. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

PARTS TO THIS DRAWING

DO NOT M	IANUFACTURE THIS DRAWING				e	Edm ur	nd Optio)S®
SHAPE	S1 PLANO	\$2 PLANO	THIRD ANGLE PROJECTION	$\phi \lhd$	TITLE	GRATING HOLO	1200GR VIS 12.5 X	25
CLEAR APERTURE	11.25 x 22.5	N/A	ALL DIMS IN	mm	DWG NO	43215		SHEET 1 OF 1