


NOTES:

- SUBSTRATE: FUSED SILICA
- COATING (APPLY ACROSS CLEAR APERTURE)
S1: R(avg) ≤1.5% @ 600 - 1050nm
S2: R(avg) ≤1.5% @ 600 - 1050nm
- EDGES: FINE GROUND
- CENTERING: <3-5 ARCMIN
- ASPHERE FIGURE ERROR: 0.75µm RMS

△ ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)



$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



COEFFICIENT TABLE △7	
COEFFICIENT	S1
k	-6.200000E-01
D	0
E	4.827700E-07
F	0
G	0
H	0
J	0
L	0

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL @ 0µm	20	 Edmund Optics®	
SHAPE	CONVEX	PLANO	BFL @ 0µm	10.4		
RADIUS	22.930	INFINITY	THIRD ANGLE PROJECTION 		TITLE	25mm DIA 0.63 NA NIR COATED, UV FUSED SILICA ASPHERIC LENS
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	90%	90%	ALL DIMS IN mm		DWG NO	67280
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				SHEET 1 OF 1