NOTES:

1. SUBSTRATE: N-BK7

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

2. SURFACE \$2 TO BE PARALLEL TO SURFACE \$1 TO WITHIN 1 ARCMIN

3. COATING (APPLY ACROSS COATING APERTURE)

S1: NONE S2: NONE

4. EDGES: FINE GROUND

 POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

TRANSMITTED WAVE FRONT OVER THE CLEAR APERTURE SHALL BE

SPHERICAL (Y⁴) +0.50λ WAVE PEAK TO VALLEY @ 587nm.

WAVE FRONT ERROR FROM IDEAL SPHERICAL FORM SHALL BE
LESS THEN ±0.0625 WAVES

ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE):

$$Z(Y) = \frac{\left(\frac{1}{RADIUS}\right)^*Y^2}{1 + \sqrt{1 - (1 + k)^*\left(\frac{1}{RADIUS}\right)^2*Y^2}} + D^*Y^2 + E^*Y^4 + F^*Y^6 + G^*Y^8 + H^*Y^{10} + J^*Y^{12} + L^*Y^{14}$$

8. APPLY AN ARROW POINTING TOWARDS THE ASPHEREIC SURFACE S2 WITH PENCIL OR PERMANENT INK

ϕ 12.50 _{.0.25} ϕ	3.00±0.20
S1-	S2 <u>6</u> <u>7</u>

COEFFIECIENT TABLE 7.		
COEFFICIENT	\$1	S2
k	0	0
D	0	0
E	0	-5.6782033E-07
G	0	0
Н	0	0
J	0	0
L	0	0

S1 S2
SHAPE PLANO PLANO
CLEAR APERTURE >85 >85
SURFACE QUALITY 60-40 60-40
BEVEL PROTECTIVE AS NEEDED PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

