



NOTES:

1. LASER CLASS: IIb
SPATIAL MODE: TEM00
2. BEAM DIAMETER(mm): 1.0 Typical
BEAM DIVERGENCE(mrad): <1 Typical
3. MODULATION FREQUENCY: 0 - 10 kHz
4. OPERATING TEMPERATURE: 15 to 35 °C
OPERATING VOLTAGE: 5.0 V
5. OUTPUT POWER: 5 mW
6. WAVELENGTH RANGE: 532 ±1 nm



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION	TITLE	5mW, 532nm Fixed Focus DPSS Alignment Laser	
ALL DIMS IN mm	DWG NO	37027	SHEET 1 OF 1