





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



CENTER WAVELENGTH CWL (nm)	532
BANDWIDTH (nm)	2
OPTICAL DENSITY OD	≥6.0
TRANSMISSION (%)	>90
SURFACE QUALITY	60-40
ANGLE OF INCIDENCE (°)	0 ±2
DURABILITY (ENVIRONMENTAL)	MIL-STD-810F Paragraphs 501.4, 502.4, AND 507.4
DURABILITY (PHYSICAL)	MIL-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, AND 4.5.5.3
OD 5 BLOCKING WAVELENGTH RANGE (nm)	447-527 & 537-699
OD 6 BLOCKING WAVELENGTH RANGE (nm)	489-524 & 540-585
RoHS	COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	532nm High Performance Laser Line Filter 25mm Dia.	
ALL DIMS IN	mm	DWG NO	64252	SHEET 1 OF 1