




- NOTES:
1. MATERIAL: II-VI OPTICAL GRADE POLYCRYSTALLINE CVD DIAMOND
 BULK ABSORPTION @ 10.6µm: <0.07cm-1
 BULK ABSORPTION @ 1µm: <1cm-1
 SCATTER @ 1µm: <0.7cm-1
 INDEX OF REFRACTION: 2.38 @ 10.6µm
 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <5 ARCMIN
 3. COATING (APPLY ACROSS CLEAR APERTURE):
 S1 & S2: NONE
 4. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
MIN CLEAR APERTURE	4.50 x 4.50	4.50 x 4.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

Edmund Optics®

5mm Square, 0.5mm Thick, Uncoated Polycrystalline CVD Diamond Window

THIRD ANGLE PROJECTION

ALL DIMS IN

mm

TITLE

DWG NO

12665

SHEET 1 OF 1