NOTES:


 SUBSTRATE: UV GRADE FUSED SILICA


COATING (APPLY ACROSS COATING APERTURE): \$1 & \$2: VIS-NIR (400-1000nm) R(ABS) ≤0.25% @ 880nm R(AVG) ≤1.25% @ 400 - 870nm R(AVG) ≤1.25% @ 890 - 1000nm

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <5 ARCSEC

4. FINE GRIND SURFACE

5. ROHS COMPLIANT





PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2]	8	Edmund Optic	S [®]
SHAPE	PLANO	PLANO		TITLE	25mm Dia., 5mm Thick, VIS-NIR Coated λ/10 Fused Silica Window	
SURFACE QUALITY	20-10	20-10	THIRD ANGLE PROJECTION			
CLEAR APERTURE	Ø20.00	Ø20.00			Toda amaa Tiiraatt	011557
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN mm	DWG NO	11890	SHEET 1 OF 1