




FOCAL LENGTH (EFL): $-25 \pm 0,25$
 BACK FOCAL LENGTH (BFL): $-26,96$

- 1 AR COATING: VIS 0°
 $R(AVG) \leq 0,4\%$ FROM 425-675nm @ 0° AOI
 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$19,62 \pm 0,02$ CV	GLASS N-SF11 785/258	R	∞ PL
Øe	24		Øe	24
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

25mm Diameter x -25 FL, VIS 0, Inked, Plano-Concave Lens

DWG NO

47911INK

SHEET SIZE
A4

SHEET
1 OF 1