




FOCAL LENGTH (EFL): 15 ±0,15
BACK FOCAL LENGTH (BFL): 13,02

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	7,75±0,008 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	8,1		Øe	8,1
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY						TITLE 9,0mm Dia, x 15,0mm FL, Uncoated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									
INDICATIONS IN ACCORDANCE WITH ISO 10110				ALL DIMS IN:	mm	DWG NO 49876		SHEET SIZE A4	SHEET 1 OF 1